

Drill Kits

These 115 drill bits come in standard jobber lengths and are constructed from the finest quality high-speed steel coated in titanium nitride, enabling them to withstand the harshest of environments. The included case is molded grey plastic. It features labeled locations for each drill bit.

Specifications

- 115-Piece Drill Bit Set
 - Molded Grey Plastic Carrying Case
 - 60 Number-Sized Drill Bits
 - 29 Fractional-Sized Drill Bits
 - 26 Letter-Sized Drill Bits
- Number-Sized Drill Bits Ranging from #1 Bit - #60 Bit
- Fractional-Sized Drill Bits Ranging from 1/16" - 1/2"
- Letter-Sized Drill Bits Ranging from Letter A Bit Through Letter Z Bit



DK2

ITEM #	\$	£	€	RMB	DESCRIPTION
DK2	\$ 97.00	£ 69.84	€ 84.39	¥ 773.09	115-Piece Drill Kit

Special Taps

Universal Tap Wrench

ITEM #	\$	£	€	RMB	DESCRIPTION
TW25	\$ 56.00	£ 40.32	€ 48.72	¥ 446.32	Tap Wrench - Fits up to 1/4" Taps
XE25TG	\$ 66.30	£ 47.74	€ 57.68	¥ 528.41	Tap Guide for 1/4"-20 Tap (Item # 71598, See Table Below)



TW25
Tap
Wrench

Imperial Taps

ITEM #	\$	£	€	RMB	THREAD	TAP DRILL	USE
99943	\$ 30.50	£ 21.96	€ 26.54	¥ 243.09	6-80	0.125"	F6SS, Fine Adjustment Screws
74580	\$ 27.40	£ 19.73	€ 23.84	¥ 218.38	3/16"-100	0.177"	F19SS, UFS, Ultra-Fine Adjustment Screws
71598	\$ 27.40	£ 19.73	€ 23.84	¥ 218.38	1/4"-20	0.201"	1/4"-20 Mounting Holes
71529	\$ 27.40	£ 19.73	€ 23.84	¥ 218.38	1/4"-80	0.238"	F25SS, FAS Fine Adjustment Screws
99940	\$ 35.70	£ 25.70	€ 31.06	¥ 284.53	1/4"-100	0.240"	F25US, Ultra-Fine Adjustment Screws
60202	\$ 28.40	£ 20.45	€ 24.71	¥ 226.35	5/16"-32	0.281"	N100L5, UFS Nuts
60242	\$ 26.40	£ 19.01	€ 22.97	¥ 210.41	3/8"-40	0.348"	FAS Nuts
83373	\$ 86.20	£ 62.06	€ 74.99	¥ 687.01	0.535"-40	0.508"	SM05 Series Threads
46720	\$ 73.60	£ 52.99	€ 64.03	¥ 586.59	0.800"-36	0.772"	RMS Microscope Threads
97355	\$ 86.20	£ 62.06	€ 74.99	¥ 687.01	1.035"-40	1.008"	SM1 Series Threads



XE25TG
Tap
Guide



TW25
Tap
Wrench

Metric Taps

ITEM #	\$	£	€	RMB	THREAD	TAP DRILL	USE
99946	\$ 35.70	£ 25.70	€ 31.06	¥ 284.53	M3 x 0.25	2.7 mm	F3SS, MAS Screws
99833	\$ 31.60	£ 22.75	€ 27.49	¥ 251.85	M4.5 x 0.5	4.0 mm	N250L3P, MAS Nuts
97368	\$ 26.40	£ 19.01	€ 22.97	¥ 210.41	M6 x 0.5	5.5 mm	M6 x 0.5 Threaded Aspheric Lens Housing
71498	\$ 25.20	£ 18.14	€ 21.92	¥ 200.84	M6 x 1.0	5.0 mm	M6 1.0 Mounting Holes
48443	\$ 30.50	£ 21.96	€ 26.54	¥ 243.09	M8 x 0.5	7.5 mm	M8 x 0.5 Threaded Aspheric Lens Housing
98109	\$ 32.60	£ 23.47	€ 28.36	¥ 259.82	M9 x 0.5	8.5 mm	M9 x 0.5 Threaded Aspheric Lens Housing
43122	\$ 46.30	£ 33.34	€ 40.28	¥ 369.01	M10 x 0.5	9.5 mm	M10 x 0.5 Threaded Aspheric Lens Housing
98110	\$ 47.40	£ 34.13	€ 41.24	¥ 377.78	M11 x 0.5	10.5 mm	M11 x 0.5 Threaded Aspheric Lens Housing
46152	\$ 44.20	£ 31.82	€ 38.45	¥ 352.27	M12 x 0.5	11.5 mm	M12 x 0.5 Threaded Aspheric Lens Housing
45283	\$ 55.70	£ 40.10	€ 48.46	¥ 443.93	M14 x 0.5	13.5 mm	E12RMS Tube External Thread
99925	\$ 135.00	£ 97.20	€ 117.45	¥ 1,075.95	M25 x 0.75	24.0 mm	M25 x 0.75 Microscope Objectives




Specialty plug taps are not readily available from tooling suppliers and are provided to aid in the integration of our components into custom-built devices.

Double-Sided Adhesive Tape

- White, Double-Sided Tape with 3M Adhesive 375
- 10.2 mil Thick, 19 mm Wide, 50 m Long
- Bonds on Contact to Almost any High and Low Surface Energy Substrate
- Bonds are Durable with High Peel and Shear Strength

This 3M tape is 10.2 mil thick and double coated with 375 adhesive. The tape features a high peel and shear strength, excellent resistance to UV light, good solvent and plasticizer resistance, and long-term temperature performance up to 158 °F (70 °C).

NEW
product



DST1950

ITEM #	\$	£	€	RMB	DESCRIPTION
DST1950	\$ 19.50	£ 14.04	€ 16.97	¥ 155.42	Double-Sided Adhesive Tape, 19 mm Wide, 50 m Long