



Stainless Steel Thread Adapters


NEW
versions




ITEM#	\$	£	€	RMB	THREAD A	THREAD B	LENGTH C
AP8E4E	\$ 1.90	£ 1.30	€ 1,70	¥ 16.10	#8-32	#4-40	0.38" (9.7 mm)
AP8E4M	\$ 1.70	£ 1.20	€ 1,50	¥ 14.40	#8-32	M4 x 0.7	0.48" (12.2 mm)
AP8E25E	\$ 1.70	£ 1.20	€ 1,50	¥ 14.40	#8-32	1/4"-20	0.57" (14.5 mm)
AP25E6M	\$ 1.70	£ 1.20	€ 1,50	¥ 14.40	1/4"-20	M6 x 1.0	0.57" (14.5 mm)
AP4M3M	\$ 1.90	£ 1.30	€ 1,70	¥ 16.10	M4 x 0.7	M3 x 0.5	0.38" (9.7 mm)
AP6M8E	\$ 1.70	£ 1.20	€ 1,50	¥ 14.40	M6 x 1.0	#8-32	0.57" (14.5 mm)
AP6M4M	\$ 1.70	£ 1.20	€ 1,50	¥ 14.40	M6 x 1.0	M4 x 0.7	0.57" (14.5 mm)



ITEM#	\$	£	€	RMB	THREAD A	THREAD B	LENGTH C
AS8E4M	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	#8-32	M4 x 0.7	0.56" (14.2 mm)
AS8E25E	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	#8-32	1/4"-20	0.68" (17.3 mm)
AS8E6M	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	#8-32	M6 x 1.0	0.68" (17.3 mm)
AS25E8E	\$ 4.70	£ 3.25	€ 4,15	¥ 39.70	1/4"-20	#8-32	0.61" (15.4 mm)
AS25E4M	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	1/4"-20	M4 x 0.7	0.61" (15.4 mm)
AS25E6M	\$ 5.10	£ 3.55	€ 4,55	¥ 43.10	1/4"-20	M6 x 1.0	0.63" (16.0 mm)
AS4M8E	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	M4 x 0.7	#8-32	0.56" (14.2 mm)
AS4M25E	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	M4 x 0.7	1/4"-20	0.68" (17.3 mm)
AS4M6M	\$ 4.70	£ 3.25	€ 4,15	¥ 39.70	M4 x 0.7	M6 x 1.0	0.68" (17.3 mm)
AS6M4M	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	M6 x 1.0	M4 x 0.7	0.61" (15.4 mm)
AS6M8E	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	M6 x 1.0	#8-32	0.61" (15.4 mm)
AS6M25E	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	M6 x 1.0	1/4"-20	0.63" (16.0 mm)




ITEM#	\$	£	€	RMB	THREAD A	THREAD B	LENGTH C
AE4E25E	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	#4-40	1/4"-20	0.38" (9.5 mm)
AE4E6M	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	#4-40	M6 x 1.0	0.39" (10.0 mm)
AE6E25E	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	#6-32	1/4"-20	0.38" (9.5 mm)
AE6E6M	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	#6-32	M6 x 1.0	0.39" (10.0 mm)
AE8E25E	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	#8-32	1/4"-20	0.38" (9.5 mm)
AE8E6M	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	#8-32	M6 x 1.0	0.39" (10.0 mm)
AE25M25E	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	M2.5 x 0.45	1/4"-20	0.38" (9.5 mm)
AE25M6M	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	M2.5 x 0.45	M6 x 1.0	0.39" (10.0 mm)
AE3M25E	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	M3 x 0.5	1/4"-20	0.38" (9.5 mm)
AE3M6M	\$ 4.10	£ 2.85	€ 3,65	¥ 34.70	M3 x 0.5	M6 x 1.0	0.39" (10.0 mm)
AE4M25E	\$ 3.60	£ 2.50	€ 3,20	¥ 30.40	M4 x 0.7	1/4"-20	0.38" (9.5 mm)
AE4M6M	\$ 3.60	£ 2.50	€ 3,20	¥ 30.40	M4 x 0.7	M6 x 1.0	0.39" (10.0 mm)



ITEM#	\$	£	€	RMB	THREAD A	THREAD B	LENGTH C
AI25E8E	\$ 4.70	£ 3.25	€ 4,15	¥ 39.70	#8-32	1/4"-20	0.50" (12.7 mm)
AI6M4M	\$ 4.70	£ 3.25	€ 4,15	¥ 39.70	M4 x 0.7	M6 x 1.0	0.50" (12.7 mm)
AI25E4M	\$ 4.70	£ 3.25	€ 4,15	¥ 39.70	M4 x 0.7	1/4"-20	0.50" (12.7 mm)

Mini-Series Thread Adapters



- Adapt Ø6 mm Posts to Other Common Thread Standards
- Ideal for Adapting Larger Optomechanic Mounts to Our Mini-Series Posts (see page 72)
- Ø0.08" (Ø2.0 mm) Hole-to-Lock/Unlock Adapter

Mechanical
Drawings Available on the
WEB



ITEM#	\$	£	€	RMB	THREAD A	THREAD B	LENGTH C
MSA8	\$ 7.99	£ 5.55	€ 7,10	¥ 67.50	#4-40	#8-32	0.50" (12.7 mm)
MSA25	\$ 7.99	£ 5.55	€ 7,10	¥ 67.50	#4-40	1/4"-20	0.55" (14.0 mm)
MSA4/M	\$ 7.99	£ 5.55	€ 7,10	¥ 67.50	M3 x 0.5	M4 x 0.7	0.50" (12.7 mm)
MSA6/M	\$ 7.99	£ 5.55	€ 7,10	¥ 67.50	M3 x 0.5	M6 x 1.0	0.55" (14.0 mm)

Please refer to our website for complete models and drawings.