

For current pricing, please see our website.

CHAPTERS

Fiber Patch Cables

Bare Fiber

Fiber Optomechanics

Fiber Components

Test and Measurement

SECTIONS

Collimators

Couplers

WDMs

RGB Combiner

Circulators

Fiber Isolators

Faraday Mirrors

Fiber Attenuators

Polarization Controllers


Optical Switches

Mating Sleeves

Terminating Connectors

Termination

## FC/PC to FC/PC Mating Sleeves




ADAFC1 Panel Mount



- **FCB1:** Two FC/PC mating sleeves premounted on an L-bracket that can be easily mounted onto a TR series post. (Wide key: 2.2 mm)
- **ADAFC1:** Use this as a panel mount (D hole) or as a floating style adapter to connect two FC single or multimode cables. (Wide key: 2.2 mm)
- **ADAFC2:** This FC/PC to FC/PC adapter has a square flange and is intended for panel mounting. The flange has two clearance holes located diagonally on a 9.50 mm square, while two additional holes are M2 x 0.4 tapped. (Wide key: 2.2 mm)

ITEM #	\$	£	€	RMB	DESCRIPTION
FCB1	\$ 54.70	£ 39.38	€ 47.59	¥ 435.96	FC/PC to FC/PC Dual Mating Sleeve L-Bracket
ADAFC1	\$ 9.60	£ 6.91	€ 8.35	¥ 76.51	FC/PC to FC/PC D Hole Mating Sleeve
ADAFC2	\$ 10.70	£ 7.70	€ 9.31	¥ 85.28	FC/PC to FC/PC Square Mating Sleeve

## FC/APC to FC/APC Mating Sleeves



- **FCB2:** Two FC/APC mating sleeves premounted on an L-bracket that can be easily mounted onto a TR series post. (Narrow key: 2.0 mm)
- **ADAFC4:** Mount this mating sleeve in the D-hole of a standard rack mount panel or use it as a floating style adapter to connect two FC/APC single mode cables. (Narrow key: 2.0 mm)
- **ADAFC3:** For use with angle-polished FC cables. This adapter can be used as a floating style or as a panel mount (D hole) to connect two single mode APC cables. (Narrow key: 2.0 mm)

ITEM #	\$	£	€	RMB	DESCRIPTION
FCB2	\$ 74.90	£ 53.93	€ 65.16	¥ 596.95	FC/APC to FC/APC Dual Mating Sleeve L-Bracket
ADAFC4	\$ 14.30	£ 10.30	€ 12.44	¥ 113.97	FC/APC to FC/APC D Hole Mating Sleeve
ADAFC3	\$ 20.80	£ 14.98	€ 18.10	¥ 165.78	FC/APC to FC/APC Square Mating Sleeve

## FC to FC PM Mating Sleeves



ADAFC2-PMW Panel Mount PM FC to PM FC 2.1 mm Key Slot

ADAFC2-PMN Panel Mount PM FC to PM FC 2.0 mm Key Slot

### Features

- Compatible with FC/PC and FC/APC Connectors
- Monolithic Design Ensures Optimal Performance for PM-PM Interfaces
- Wide (2.09-2.14 mm) and Narrow (1.97-2.02 mm) Key Versions

The ADAFC2-PMN and ADAFC2-PMW mating sleeves have a monolithic construction and square flange that allows them to be attached to a panel. They are ideal for joining polarization-maintaining fibers with FC/PC or FC/APC connectors. ADAFC2-PMN has a 2.0 mm (narrow) keyway, while the ADAFC2-PMW has a 2.1 mm (wide) keyway.


ITEM #	\$	£	€	RMB	DESCRIPTION
ADAFC2-PMN	\$ 48.00	£ 34.56	€ 41.76	¥ 382.56	PM FC Adapter Narrow (2.0 mm) Key
ADAFC2-PMW	\$ 48.00	£ 34.56	€ 41.76	¥ 382.56	PM FC Adapter Wide (2.1 mm) Key

## SMA to SMA Mating Sleeves



ADASMA Panel Mount

SMAB1 L-Bracket



- The ADASMA Mating Sleeve and SMAB1 Dual L-Bracket are designed to connect SMA-terminated fibers. Although the ADASMA is compatible with SMA905-style connectors, an adapter is included that allows the mating sleeve to be used with SMA906-connectorized fibers.
- The SMAB1 Dual L-Bracket consists of two ADASMA mating sleeves that have been premounted on an L-bracket. The bracket can be mounted on a TR Series Post (See Page 93).

ITEM #	\$	£	€	RMB	DESCRIPTION
ADASMA	\$ 17.30	£ 12.46	€ 15.05	¥ 137.88	SMA to SMA Mating Sleeve
SMAB1	\$ 39.50	£ 28.44	€ 34.37	¥ 314.82	SMA to SMA Dual L-Bracket Mating Sleeve