


43 Sparta Avenue Newton, NJ 07860

LC5893-E - April 3, 2024

Item # LC5893-E was discontinued on April 3, 2024. For informational purposes, this is a copy of the website content at that time and is valid only for the stated product.

CALCIUM FLUORIDE PLANO-CONCAVE LENSES, AR-COATED: 2 - 5 MM



OVERVIEW

Features

- Vacuum-Grade Calcium Fluoride
 Substrate
- Ø1/2" and Ø1" Versions Available
 Broadband AR Coating for the 2 -
- 5 μm Range
- Focal Lengths from -18.0 mm to -500.0 mm

Thorlabs' Ø1/2" and Ø1" Calcium Fluoride (CaF₂) Plano-Concave Lenses

have a broadband AR coating optimized for the 2 μ m to 5 μ m spectral range deposited on both surfaces. This coating greatly reduces the surface reflectivity of the substrate, yielding an average transmission in excess of 97% over the entire AR coating range. See the *Graphs* tab for detailed information.

CaF₂ is commonly used for applications requiring

high transmission in the infrared and ultraviolet spectral ranges. The material exhibits a low refractive index, varying from 1.35 to 1.51 within



E Zemax Files

Click on the red Document

icon next to the item

numbers below to access

the Zemax file download

Our entire Zemax Catalog is

also available.

its usage range of 180 nm to 8.0 $\mu m.$ Calcium fluoride is also fairly chemically

Common Spec	ifications			
Substrate Material	Vacuum-Grade Calcium Fluoride ^a			
AR Coating Range	2 - 5 µm			
Reflectance over Coating Range (Avg.)	<1.25%			
Diameters Available	1/2" or 1"			
Diameter Tolerance +0.0/-0.1 mm				
Thickness Tolerance ±0.1 mm				
Focal Length Tolerance	±1%			
Surface Quality	40-20 Scratch-Dig			
Surface Flatness (Plano Side)	λ/2			
Spherical Surface Power (Concave Side) ^b	3λ/2			
Surface Irregularity (Peak to Valley)	λ/2			
Centration	<3 arcmin			
Clear Aperture	>90% of Diameter			
Design Wavelength	588 nm			

Thorlabs.com - Calcium Fluoride Plano-Concave Lenses, AR-Coated: 2 - 5 µm


inert and offers superior hardness compared to its barium fluoride, magnesium fluoride, and lithium fluoride cousins.

Like all plano-concave lenses, these lenses have negative focal lengths and can be used to diverge collimated beams; in this case, the curved surface should face the source in order to minimize spherical aberration. In addition, they can be employed to offset the effects of spherical aberration caused by other lenses in an optical system.

- Click Link for Detailed Specifications on the Substrate
- Much like surface flatness for flat optics, spherical surface power is a measure of the deviation between the surface of the curved optic and a calibrated reference gauge, typically for a 633 nm source, unless otherwise stated. This specification is also commonly referred to as surface fit.

See the tables below for individual lens specifications. These lenses are also available uncoated.





Thorlabs.com - Calcium Fluoride Plano-Concave Lenses, AR-Coated: 2 - 5 µm

Wavelength (µm)	Total Transmission	Wavelength (µm)	Total Transmission	Wavelength (µm)	Total Transmission	Wavelength (µm)	Total Transmission
0.2	0.910	2.2	0.939	4.2	0.943	6.2	0.947
0.4	0.929	2.4	0.939	4.4	0.943	6.4	0.947
0.6	0.935	2.6	0.940	4.6	0.943	6.6	0.948
0.8	0.937	2.8	0.940	4.8	0.944	6.8	0.949
1.0	0.938	3.0	0.940	5.0	0.945	7.0	0.949
1.2	0.938	3.2	0.941	5.2	0.945	7.2	0.948
1.4	0.938	3.4	0.941	5.4	0.945	7.4	0.947
1.6	0.938	3.6	0.941	5.6	0.946	7.6	0.946
1.8	0.939	3.8	0.942	5.8	0.946	7.8	0.945
2.0	0.939	4.0	0.942	6.0	0.947	8.0	0.944

FOCAL LENGTH SHIFT

Wavelength-Dependent Focal Length Shift

The paraxial focal length of a lens is wavelength dependent. The focal length listed below for a given lens corresponds to the value at the design wavelength (i.e., the focal length at 588 nm). Since CaF_2 offers high transmission from 0.18 - 8.0 μ m, users may wish to use these lenses at other popular wavelengths. Click on the icons below to view theoretically-calculated focal length shifts for wavelengths within the 0.18 - 8.0 μ m range.

The blue shading indicates the region for which the AR coating is optimized. Please see the Graphs tab for more information.

Ø1/2" Plano-Concave Lenses

Item #	LC5919-E	LC5749-E
Focal Length @ 588 nm	-18.0 mm	-25.0 mm
Focal Length Shift (Click for Details)		5
Raw Data (Click to Download)	Data	Data

Ø1" Plano-Concave Lenses

Item #	LC5269-E	LC5401-E	LC5289-E	LC5952-E	LC5893-E
Focal Length @ 588 nm	-40.0 mm	-75.0 mm	-100.0 mm	-200.0 mm	-500.0 mm
Focal Length Shift (Click for Details)	5	5	5	5	5
Raw Data (Click to Download)	Data	Data	Data	Data	Data

MOUNTING OPTIONS





LMR1 Fixed Mount with Ø1" Lens Click to Enlarge CXY1A Translation Mount and SM1 Lens Tube Mounted in a 30 mm Cage System



Click to Enlarge LM2XY Translating Mount with Ø2" Lens



Click to Enlarge Ø1" Optic Mounted in a ST1XY-S XY Translator

		Recommended Mounting Options for Thorlabs Lenses					
	m #	Mounts for Ø2 mm to Ø10 mm Optics					
Imperial	Metric						
	rious)	Fixed Lens Mounts and Mini-Series Fixed Lens Mounts for Small Optics, Ø5 mm to Ø10 mm					
(Vai	rious)	Small Optic Adapters for Use with Standard Fixed Lens Mounts, Ø2 mm to Ø10 mm					
lte	m #	Mounts for Ø1/2" (Ø12.7 mm) Optics					
Imperial	Metric						
LMR05	LMR05/M	Fixed Lens Mount for Ø1/2" Optics					
MLH05	MLH05/M	Mini-Series Fixed Lens Mount for Ø1/2" Optics					
LM05XY	LM05XY/M	Translating Lens Mount for Ø1/2" Optics					
SCP05		16 mm Cage System, XY Translation Mount for Ø1/2" Optics					
(Various)		Ø1/2" Lens Tubes,					
(vai	ious)	Optional SM05RRC Retaining Ring for High-Curvature Lenses (See Below)					
Item #		Mounts for Ø1" (Ø25.4 mm) Optics					
Imperial	Metric						
LMR1	LMR1/M	Fixed Lens Mount for Ø1" Optics					
LM1XY LM1XY/M Translating I		Translating Lens Mount for Ø1" Optics					
ST1XY-S ST1XY-S/M		Translating Lens Mount with Micrometer Drives (Other Drives Available)					
CX	Y1A	30 mm Cage System, XY Translation Mount for Ø1" Optics					
0.4		Ø1" Lens Tubes,					
(vai	rious)	Optional SM1RRC Retaining Ring for High-Curvature Lenses (See Below)					
Ite	m #	Mount for <i>O</i> (1 5" Ontion					
Imperial	Metric	Mount for Ø1.5" Optics					
LMR1.5	LMR1.5/M	Fixed Lens Mount for Ø1.5" Optics					
() (a)	riqua)	Ø1.5" Lens Tubes,					
(Val	rious)	Optional SM1.5RR Retaining Ring for Ø1.5" Lens Tubes and Mounts					
lte	m #	Mounts for Ø2" (Ø50.8 mm) Optics					
Imperial	Metric						
LMR2	LMR2/M	Fixed Lens Mount for Ø2" Optics					
LM2XY	LM2XY/M	Translating Lens Mount for Ø2" Optics					
C>	KY2	60 mm Cage System, XY Translation Mount for Ø2" Optics					
0.4	rique)	Ø2" Lens Tubes,					
(Vai	rious)	Optional SM2RRC Retaining Ring for High-Curvature Lenses (See Below)					
lte	m #	Adjustable Optic Mounto					
Imperial	Metric	Adjustable Optic Mounts					

Thorlabs.com - Calcium Fluoride Plano-Concave Lenses, AR-Coated: 2 - 5 µm

LH1	LH1/M	Adjustable Mount for Ø0.28" (Ø7.1 mm) to Ø1.80" (Ø45.7 mm) Optics
LH2	LH2/M	Adjustable Mount for Ø0.77" (Ø19.6 mm) to Ø2.28" (Ø57.9 mm) Optics
VG100	VG100/M	Adjustable Clamp for Ø0.5" (Ø13 mm) to Ø3.5" (Ø89 mm) Optics
SCL03	SCL03/M	Self-Centering Mount for Ø0.15" (Ø3.8 mm) to Ø1.77" (Ø45.0 mm) Optics
SCL04	SCL04/M	Self-Centering Mount for Ø0.15" (Ø3.8 mm) to Ø3.00" (Ø76.2 mm) Optics
LH160C	LH160C/M	Adjustable Mount for 60 mm Cage Systems, Ø0.50" (Ø13 mm) to Ø2.00" (Ø50.8 mm) Optics
SCL60C	SCL60C/M	Self-Centering Mount for 60 mm Cage Systems, Ø0.15" (Ø3.8 mm) to Ø1.77" (Ø45.0 mm) Optics

Mounting High-Curvature Optics

Thorlabs' retaining rings are used to secure unmounted optics within lens tubes or optic mounts. These rings are secured in position using a compatible spanner wrench. For flat or low-curvature optics, standard retaining rings manufactured from anodized aluminum are available from Ø5 mm to Ø4". For high-curvature optics, extra-thick retaining rings are available in Ø1/2", Ø1", and Ø2" sizes.

Extra-thick retaining rings offer several features that aid in mounting high-curvature optics such as aspheric lenses, short-focal-length plano-convex lenses, and condenser lenses. As shown in the animation to the right, the guide flange of the spanner wrench will collide with the surface of high-curvature lenses when using a standard retaining ring, potentially scratching the optic. This contact also creates a gap between the spanner wrench and retaining ring, preventing the ring from tightening correctly. Extra-thick retaining rings provide the necessary clearance for the spanner wrench to secure the lens without coming into contact with the optic surface.

Ø1/2" CaF2 Plano-Concave Lenses, AR-Coated: 2 - 5 µm

Item #	Diameter	Focal Length	Diopter ^a	Radius of Curvature	Center Thickness	Edge Thickness ^b	Back Focal Length ^c	Reference Drawing
LC5919-E ^d	1/2" (12.7 mm)	-18.0 mm	-55.6	-7.8 mm	2.0 mm	5.3 mm	-19.4 mm	•
LC5749-E ^e	1/2" (12.7 mm)	-25.0 mm	-40.0	-10.8 mm	2.5 mm	4.6 mm	-26.7 mm	•

a. Reciprocal of the Focal Length in Meters

b. Edge Thickness Given Before 0.2 mm at 45°

c. Typical Chamfer Measured at the Design Wavelength, 588 nm

d. Suggested Fixed Lens Mounts: LMR05(/M) & SM05L03

e. Suggested Fixed Lens Mount: LMR05(/M)

Part Number	Description	Price	Availability
LC5919-E	Ø1/2" CaF ₂ Plano-Concave Lens, f = -18.0 mm, AR-Coated: 2 - 5 µm	\$197.20	Today
LC5749-E	Ø1/2" CaF ₂ Plano-Concave Lens, f = -25.0 mm, AR-Coated: 2 - 5 μm	\$185.31	Today

Ø1" CaF₂ Plano-Concave Lenses, AR-Coated: 2 - 5 µm

Item #	Diameter	Focal Length	Diopter ^a	Radius of Curvature	Center Thickness	Edge Thickness ^b	Back Focal Length ^c	Reference Drawing
LC5269-E ^d	1" (25.4 mm)	-40.0 mm	-25.0	-17.4 mm	2.0 mm	7.5 mm	-41.4 mm	
LC5401-E ^e	1" (25.4 mm)	-75.0 mm	-13.3	-32.5 mm	2.5 mm	5.1 mm	-76.8 mm	
LC5289-E ^e	1" (25.4 mm)	-100.0 mm	-10.0	-43.4 mm	3.0 mm	4.9 mm	-102.1 mm	0
LC5952-E ^e	1" (25.4 mm)	-200.0 mm	-5.0	-86.8 mm	3.5 mm	4.4 mm	-202.4 mm	

Thorlabs.com - Calcium Fluoride Plano-Concave Lenses, AR-Coated: 2 - 5 μm

a.	Reciprocal of th	e Focal Length ir	Meters					
b.	Edge thickness	given before 0.2	mm at 45° typ	ical chamfer.				
c. Measured at the design wavelength, 588 nm.								
d.	Suggested Fixe	d Lens Mounts: L	MR1(/M) & S	M1L05				
e. Suggested Fixed Lens Mount: LMR1(/M)								

Part Number	Description	Price	Availability
LC5269-E	Ø1" CaF ₂ Plano-Concave Lens, f = -40.0 mm, AR-Coated: 2 - 5 μm	\$256.59	Today
LC5401-E	Ø1" CaF ₂ Plano-Concave Lens, f = -75.0 mm, AR-Coated: 2 - 5 μm	\$244.70	Today
LC5289-E	Ø1" CaF ₂ Plano-Concave Lens, f = -100.0 mm, AR-Coated: 2 - 5 μm	\$238.78	Today
LC5952-E	Ø1" CaF ₂ Plano-Concave Lens, f = -200.0 mm, AR-Coated: 2 - 5 μm	\$230.46	Today
LC5893-E	Ø1" CaF ₂ Plano-Concave Lens, f = -500.0 mm, AR-Coated: 2 - 5 μm	\$224.51	Today

