

FINAL INSPECTION REPORT

1x2 200 µm Core 50:50 Multimode Coupler

Item #: TM200FS1B

SN: T034942

Bandwidth: 400 - 2200 nm

Coupling Ratio Specification

Signal Output: 45 % - 55 %

Tap Output: 45 % - 55 %

Maximum Optical Power^a

With Connectors or Bare Fiber: 5 W

Spliced: 10 W

Fiber Type: Thorlabs Custom 0.22 NA MM Fiber

Test Data ^b	
Excess Loss ^c	≤ 0.6 dB
Input-Output Path	Black (Input) - White (Signal Output)
Coupling Ratio ^d	51.5 %
Insertion Loss ^e	3.24 dB
Input-Output Path	Black (Input) - Red (Tap Output)
Coupling Ratio ^d	48.5 %
Insertion Loss ^e	3.49 dB

- a. Specifies the maximum power allowed through the component. Performance and reliability under high power conditions must be determined within the user's setup.
- b. All values are measured at room temperature at 650 nm without connectors through the black input port.
- c. Ratio of the input optical power to the total optical power from all output ports. It is measured at the specified wavelength.
- d. Does not include losses, as this is a measurement of the output power distribution only.
- e. Includes both the split of the power between the two outputs, as well as any optical losses in the coupler.

