

FINAL INSPECTION REPORT

1x2 200 μ m Core 90:10 Multimode Coupler

Item #: TM200R2S1B
SN: T028151

Bandwidth: 400 - 2200 nm
Coupling Ratio Specification
Signal Output: 88.5 % - 91.5 %
Tap Output: 8.5 % - 11.5 %
Maximum Optical Power^a
With Connectors or Bare Fiber: 5 W
Spliced: 10 W
Fiber Type: Thorlabs Custom 0.22 NA MM Fiber

| Test Data ^b | |
|-----------------------------|---------------------------------------|
| Excess Loss ^c | ≤ 0.5 dB |
| Input-Output Path | White (Input) – White (Signal Output) |
| Coupling Ratio ^d | 89.9 % |
| Insertion Loss ^e | 0.56 dB |
| Input-Output Path | White (Input) – Red (Tap Output) |
| Coupling Ratio ^d | 10.1 % |
| Insertion Loss ^e | 10.05 dB |

a. Specifies the maximum power allowed through the component. Performance and reliability under high power conditions must be determined within the user's setup.

b. All values are measured at room temperature at 650 nm without connectors through the white input port.

c. Ratio of the input optical power to the total optical power from all output ports. It is measured at the specified wavelength.

d. Does not include losses, as this is a measurement of the output power distribution only.

e. Includes both the split of the power between the two outputs, as well as any optical losses in the coupler.

Verified by: _____